

HydroSol Latex Settings for HP L26500/L28500/260/280

	165SML	180STL				153SBB		
	250STW	195SMSD				164SMB		
	300SVW	130SSRP	230STL	290SML	210SPS	385STL	215SMB	225STFG
Generic Setting	HP photorealistic	HP photorealistic	HP photorealistic	HP photorealistic	HP Photorealistic poster paper	HP photorealistic	backlit	tyvek
Dry	53	55	53	53	55	55	55	55
Cure	76	85	82	85	77	90	76	100
Ink Level	standard	standard	standard	standard	standard	standard	High	High
No. Passes *	12-pass	10-pass	16-pass	12-pass	10 pass	16-pass	20-pass	12-pass
	bi-directional	bi-directional	bi-directional	bi-directional	Bi-directional	bi-directional	bi-directional	bi-directional
Vacuum	30	25	30	30	25	25	25	25
Input	15	15	15	15	15	15	15	15
Drying power	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4
Air flow	35	30	35	35	30	30	20	30
OMAS	off	on	off	off	on	off	on	on